



Multi-purpose soldering iron, Heating power: 80W



Order data

Order number	082100 80
GTIN	4003008069471
Item class	04C

Description

Version:

Tough industrial soldering irons with **Ersadur long-life soldering tips** (30 times the working life of conventional copper soldering tips). **Warm-up time 3 min.** (for size 300, approx. 5 min.). Power cable 1.5 m rubber cable (PVC for size 30). **With support stand** (not size 30).

Technical description

Weight without power lead	220 g
Heating power	80 W
suitable for copper cross sections up to	4 mm ²
Soldering tip width	4.8 mm
Soldering tip temperature after 3 minutes	410 °C
Power supply	Mains operated
Type of product	Soldering iron

Accessories

Lead-free soldering wire Sn96.5, Ag3.0, Cu0.5, roll of 250 g Soldering wire Ø 1,5 mm	082365 1,5
Soldering tip Manufacturer's designation 82JD	082400 82JD
Desoldering pump PDD03 plastic, antistatic	082355

Lead-free soldering wire Sn96.5, Ag3.0, Cu0.5, roll of 250 g
Soldering wire Ø 1 mm

082365 1