



## Indexable drill holder Form E1, VDI 40, Bore d<sub>2</sub> (H6): 40 mm



### Order data

Order number	319250 40
GTIN	4045197191199
Item class	32V

### Description

#### Application:

For drilling with indexable drill with internal coolant supply.

#### Standard:

**DIN 69880 / VDI 3425**, Blatt 2.

Shape: E

Colour code for VDI shanks: VDI 40

External Ø d<sub>3</sub>: 65 mm

l<sub>1</sub> -0.2: 90 mm

l<sub>2</sub>: 73 mm

### Technical description

External Ø d <sub>3</sub>	65 mm
l <sub>1</sub> -0.2	90 mm
l <sub>2</sub>	73 mm
Bore d <sub>2</sub> (H6)	40 mm
Shape	E
VDI size	VDI 40
d <sub>6</sub>	83 mm
Colour code for VDI shanks	VDI 40

Type of product

VDI tool arbor