

**Reducing adapter, Shank \varnothing d1 / clamping \varnothing d2: 25/20mm****Order data**

Order number	319426 25/20
GTIN	4045197586643
Item class	32V

Description**Version:**

Suitable for VDI arbors form E2 (No. 319275 – 319405).

Suitable for internal cooling, not slotted. Tool is fixed and clamped with 2 clamping screws.

Application:

For \varnothing reduction for tools with plain shanks.

Technical description

l_2	4 mm
Version	Slot
$\varnothing d_4$	29 mm
l_1	50 mm
Clamping range $\varnothing d_2$	20 mm
Shank $\varnothing D_1$	25 mm
Type of product	Reducing adapter