

SWISS TOOLS

Screw-on boring bar left-hand, PSC, Shank \varnothing / insert size – A dimension: 40/11-90mm



Order data

Order number	320396 40/11-90
GTIN	2050001715456
Item class	36D

Description

Note:

Order the suitable **HP nozzle** No. 320001 separately. Spare parts No. 320610 – 320626 can be found in the spare parts list.
PSC clamping stud on request.

Technical description

Overhang dimension A	90 mm
Axis tip distance f	17 mm
suitable indexable insert	DC.. 11T3..
Spare part	S05
Insert size	11
Minimum pre-drill $\varnothing D_1$ min	32 mm
Shank \varnothing	40 mm
Usable length L_N	70 mm
Adapter	PSC
Application type	left-hand
Arbor standard	ISO 26623-1

Through-coolant	yes
Setting angle κ	107.5 degrees
Type of product	boring bar holder

Accessories

Clamping screw No. 3 Type P02	320611 P02
High-pressure cooling nozzle (HP) Type 63	320001 63
Intermediate spacer No. 1 Type P05	320610 P05
Toggle lever No. 4 Type P05	320612 P05
Intermediate spacer No. 1 Type P01	320610 P01
Nozzle ring No. 5 Type D07	320613 D07
Clamping screw No. 3 Type P06	320611 P06
Intermediate spacer No. 1 Type P06	320610 P06
Tube pin No. 7 Type P02	320618 P02
Tube pin No. 7 Type P01	320618 P01
Tube pin No. 7 Type P04	320618 P04
Clamping screw No. 3 Type P05	320611 P05
Intermediate spacer No. 1 Type P04	320610 P04
Toggle lever No. 4 Type P01	320612 P01
Tube pin No. 7 Type P06	320618 P06
Toggle lever No. 4 Type P04	320612 P04
Clamp No. 6 Type D07	320614 D07
Clamping screw No. 3 Type D07	320611 D07
Toggle lever No. 4 Type P06	320612 P06
Tube pin No. 7 Type P05	320618 P05
Intermediate spacer No. 1 Type P02	320610 P02
Toggle lever No. 4 Type P02	320612 P02
Clamping screw No. 3 Type P01	320611 P01

