

Garant
Shrink-fit chuck, PSC 63 A = 120, Clamping range \varnothing D1: 12mm

Order data

Order number	308571 12
GTIN	4045197471925
Item class	31C

Description
Version:

- **With RFID/Balluffchip bore.**
- **All shanks hard turned (for smooth running!).**
- **Mating faces of the PSC internal contour machined.**

Application:

For clamping tools with shank tolerance h6.

Optional extras:

Shrink-fit chuck extensions No. 302410 – 302417. Shrink-fit units No. 354210 – 354450.
Coolant tube No. 309885; socket No. 309893 and balancing screw set No. 309906 size 180.

Technical description

\varnothing D ₂	24 mm
Overhang dimension A	120 mm
Clamping \varnothing D ₁	12 mm
External \varnothing D	32 mm
Adapter	PSC 63 A = 120
Arbor standard	ISO 26623-1
Through-coolant	yes
Balance quality G at rotational speed	G 2.5 at 25,000 rpm

Concentricity	≤ 3 μm
Machining strategy	HPC
Machining strategy	HSC
Type of product	Shrink-fit chuck

Accessories

Shrink-fit unit Type SU1	354210 SU1
Cooling unit Type CU1	354215 CU1
Screening plate for coilSU1 for clamping Ø 6-12 mm	354240 6-12
Cooling adapter short4.5° for clamping Ø 9,1-12 mm	354235 9,1-12
Subframe cupboard	354290
Cooling adapter long4.5° for clamping Ø 9,1-12 mm	354236 9,1-12