



High-performance self-tightening drill chuck Spiro, Type: 160/16



Order data

| | |
|--------------|---------------|
| Order number | 341010 160/16 |
| GTIN | 4019208009438 |
| Item class | 39R |

Description

Version:

High performance precision three-jaw drill chucks. High concentricity, keyless, self-tightening, high clamping force. Easily released by hand. Wearing parts hardened and exchangeable.

Application:

For bench and pillar drilling machines, milling machines, lathes, for use with arbors No. 342300 – 342850 or directly on machine spindles.

Standard:

DIN 238

Technical description

| | |
|---|---------------------|
| Type | 160/16 |
| Drill head length closed | 109 mm |
| Drill chuck taper | B 16 |
| Clamping range | 3 - 16 mm |
| largest drill chuck taper \varnothing | 15.733 mm |
| Drill head length open | 95.5 mm |
| External \varnothing | 56 mm |
| Type of product | Drill chuck keyless |

