



## High-performance self-tightening drill chuck Spiro, Type: 160/18



### Order data

Order number	341010 160/18
GTIN	4019208009445
Item class	39R

### Description

#### Version:

**High performance** precision three-jaw drill chucks. High concentricity, keyless, self-tightening, high clamping force. Easily released by hand. Wearing parts hardened and exchangeable.

#### Application:

For bench and pillar drilling machines, milling machines, lathes, for use with arbors No. 342300 – 342850 or directly on machine spindles.

#### Standard:

**DIN 238**

### Technical description

Clamping range	3 - 16 mm
Drill chuck taper	B 18 stub
largest drill chuck taper Ø	17.431 mm
Drill head length open	95.5 mm
Drill head length closed	109 mm
Type	160/18
External Ø	56 mm
Type of product	Drill chuck keyless

