

**ALBRECHT**  
Präzisions Spannfutter

## High-performance self-tightening drill chuck, Type: 160/16



### Order data

|              |               |
|--------------|---------------|
| Order number | 341000 160/16 |
| GTIN         | 4045197308351 |
| Item class   | 33A           |

### Description

**Version:**

**High performance** precision three-jaw drill chucks. High concentricity, keyless, self-tightening, high clamping force. Easily released by hand. Wearing parts hardened and exchangeable.

**Application:**

For bench and pillar drilling machines, milling machines, lathes, for use with arbors No. 342300 – 342850 or directly on machine spindles.

**Standard:**

**DIN 238**

### Technical description

|                             |                     |
|-----------------------------|---------------------|
| Clamping range              | 3 - 16 mm           |
| Drill chuck taper           | B 16                |
| Drill head length closed    | 109 mm              |
| Type                        | 160/16              |
| largest drill chuck taper Ø | 15.733 mm           |
| Drill head length open      | 95.5 mm             |
| External Ø                  | 56 mm               |
| Type of product             | Drill chuck keyless |

