

**3M****adhesive tape, Width×length (mm× m): 50X25**

## Order data

|              |               |
|--------------|---------------|
| Order number | 083628 50X25  |
| GTIN         | 8000280457008 |
| Item class   | 08M           |

## Description

**Version:**

The **3M™ 9191** is a double-sided adhesive tape and is characterised by a **pressure-sensitive** synthetic rubber adhesive with high bonding strength and instant tack.

**Note:**

The specified "best before" date for 3M™ products is in relation to compliance with the specified storage guidelines.

Type of adhesive tape: double-sided

Adhesive: Synthetic rubber

Thickness: 0.26 mm

## Technical description

|                            |                   |
|----------------------------|-------------------|
| Colour                     | yellowish         |
| Width                      | 50 mm             |
| Length                     | 25 m              |
| Manufacturer's designation | 9191              |
| Material of covering       | Siliconised paper |

|                             |                     |
|-----------------------------|---------------------|
| Adhesive                    | Synthetic rubber    |
| Type of adhesive tape       | double-sided        |
| Liner present               | no                  |
| Special features            | can be torn by hand |
| Storage humidity            | 40 - 65 %           |
| "Best before" date          | 12 mo               |
| Thickness                   | 0.26 mm             |
| Application                 | Assembly            |
| Application                 | Lay the carpet      |
| Storage temperature         | 16 - 25 °C          |
| temperature-resistant up to | -30 - 75 °C         |
| Backing material            | Fabric              |
| Adhesive strength on steel  | 0.95 N/mm           |
| Tensile strength            | 2.6 N/mm            |
| Stretch capability          | 9 %                 |
| Type of product             | Adhesive tape       |