

ALBRECHT
Präzisions Spannfutter**High-performance self-tightening drill chuck, Type: 160/18****Order data**

Order number	341000 160/18
GTIN	4045197308368
Item class	33A

Description**Version:**

High performance precision three-jaw drill chucks. High concentricity, keyless, self-tightening, high clamping force. Easily released by hand. Wearing parts hardened and exchangeable.

Application:

For bench and pillar drilling machines, milling machines, lathes, for use with arbors No. 342300 – 342850 or directly on machine spindles.

Standard:

DIN 238

Technical description

Drill head length open	95.5 mm
Drill head length closed	109 mm
Type	160/18
largest drill chuck taper \varnothing	17.431 mm
Clamping range	3 - 16 mm
Drill chuck taper	B 18 stub
External \varnothing	56 mm
Type of product	Drill chuck keyless

