



High-performance self-tightening drill chuck Spiro, Type: 65/10



Order data

Order number	341010 65/10
GTIN	4019208198071
Item class	39R

Description

Version:

High performance precision three-jaw drill chucks. High concentricity, keyless, self-tightening, high clamping force. Easily released by hand. Wearing parts hardened and exchangeable.

Application:

For bench and pillar drilling machines, milling machines, lathes, for use with arbors No. 342300 – 342850 or directly on machine spindles.

Standard:

DIN 238

Technical description

Clamping range	0.5 - 6.5 mm
Type	65/10
Drill chuck taper	B 10
Drill head length open	61.5 mm
Drill head length closed	68 mm
largest drill chuck taper \varnothing	10.094 mm
External \varnothing	34 mm
Type of product	Drill chuck keyless

