



## Bench grinder DS with dust extraction, 400 V, Type: DS07/200A



### Order data

Order number	077514 DS07/200A
GTIN	2050001674111
Item class	03S

### Description

#### Version:

Double-ended bench grinding machine with extraction system incorporated in the base. Grinding dust is effectively collected by a water filter and downstream plastic coarse filter and fine filter. **Supplied without grinding wheels.**

#### Note:

Suitable grinding wheels can be found from No. 596100.

Power consumption: 500 W

maximum speed: 2900 min<sup>-1</sup>

Abrasive disc Ø D: 200 mm

Abrasive disc width T: 25 mm

Abrasive disc hole Ø H: 51 mm

Extraction conveying volume: 6 m<sup>3</sup>/min

### Technical description

Power consumption	500 W
Weight	95 kg

maximum speed	2900 min <sup>-1</sup>
Extraction conveying volume	6 m <sup>3</sup> /min
Manufacturer's designation	DS07/200A
Abrasive disc width T	25 mm
Abrasive disc hole Ø H	51 mm
Abrasive disc Ø D	200 mm
Power supply	Mains operated
Type of product	Double grinding machine

## Accessories

Bench grinding wheel D×T×H (mm) Type EK80	596350 EK80
Bench grinding wheel D×T×H (mm) Type NK36	596350 NK36
Bench grinding wheel D×T×H (mm) Type NK60	596400 NK60
Bench grinding wheel D×T×H (mm) Type SC80	596400 SC80
Bench grinding wheel D×T×H (mm) Type EK60	596400 EK60
Bench grinding wheel D×T×H (mm) Type SC80	596350 SC80
Bench grinding wheel D×T×H (mm) Type NK60	596350 NK60
Bench grinding wheel D×T×H (mm) Type C800	596350 C800
Bench grinding wheel D×T×H (mm) Type EK60	596350 EK60