

**ALBRECHT**  
Präzisions Spannfutter

## High-performance self-tightening drill chuck, Type: 30



### Order data

Order number	341000 30
GTIN	4045197308269
Item class	33A

### Description

**Version:**

**High performance** precision three-jaw drill chucks. High concentricity, keyless, self-tightening, high clamping force. Easily released by hand. Wearing parts hardened and exchangeable.

**Application:**

For bench and pillar drilling machines, milling machines, lathes, for use with arbors No. 342300 – 342850 or directly on machine spindles.

**Standard:**

**DIN 238**

### Technical description

Type	30
Drill head length open	44 mm
Drill chuck taper	B 10
largest drill chuck taper $\varnothing$	10.094 mm
Clamping range	0.2 - 3 mm
Drill head length closed	47.5 mm
External $\varnothing$	24 mm
Type of product	Drill chuck keyless

