



## Tap extension, Type: 12



### Order data

|              |               |
|--------------|---------------|
| Order number | 338400 12     |
| GTIN         | 4045197422989 |
| Item class   | 32H           |

### Description

#### Version:

- Long and extra long version.
- The front end of the extension acts as a collet. The collet is clamped to the tap by hand-tightening the knurled clamping nut.
- The drive torque is transmitted via the square drive.
- The rear part of the extension is to DIN, so that the extension can be mounted in quick-change tapping collets or ER tapping collets with a square drive.

#### Application:

For tapping in inaccessible places such as recesses, offsets, sharp edges on jigs, extremely deep internal threads or directly into casting walls.

#### Note:

Alternative hexagon collet for fixing the tap available on request.

### Technical description

|                                                  |        |
|--------------------------------------------------|--------|
| Extension $\varnothing D_4$                      | 22 mm  |
| Extension $L_2$                                  | 90 mm  |
| Extension $K_2$                                  | 12 mm  |
| for square $K_1$                                 | 12 mm  |
| for thread shank $\varnothing d_2$               | 16 mm  |
| for clamping length $l_1$                        | 41 mm  |
| Extension $\varnothing D_3$                      | 16 mm  |
| for thread nominal $\varnothing d_1$ DIN 374/376 | M20    |
| Extension $L_3$                                  | 200 mm |

Type of product

Extension