

**ALBRECHT**  
Präzisions Spannfutter**High-performance self-tightening drill chuck, Type: 65/10****Order data**

Order number	341000 65/10
GTIN	4045197308290
Item class	33A

**Description****Version:**

**High performance** precision three-jaw drill chucks. High concentricity, keyless, self-tightening, high clamping force. Easily released by hand. Wearing parts hardened and exchangeable.

**Application:**

For bench and pillar drilling machines, milling machines, lathes, for use with arbors No. 342300 – 342850 or directly on machine spindles.

**Standard:**

**DIN 238**

**Technical description**

Type	65/10
Drill chuck taper	B 10
Drill head length closed	68 mm
Drill head length open	61.5 mm
largest drill chuck taper $\varnothing$	10.094 mm
Clamping range	0.5 - 6.5 mm
External $\varnothing$	34 mm
Type of product	Drill chuck keyless

