



## High-performance self-tightening drill chuck Spiro, Type: 100/16



### Order data

|              |               |
|--------------|---------------|
| Order number | 341010 100/16 |
| GTIN         | 4019208196534 |
| Item class   | 39R           |

### Description

#### Version:

**High performance** precision three-jaw drill chucks. High concentricity, keyless, self-tightening, high clamping force. Easily released by hand. Wearing parts hardened and exchangeable.

#### Application:

For bench and pillar drilling machines, milling machines, lathes, for use with arbors No. 342300 – 342850 or directly on machine spindles.

#### Standard:

**DIN 238**

### Technical description

|   |                     |
|---|---------------------|
| Drill chuck taper                       | B 16                |
| Drill head length closed                | 91.5 mm             |
| Drill head length open                  | 80 mm               |
| Type                                    | 100/16              |
| Clamping range                          | 0.5 - 10 mm         |
| largest drill chuck taper $\varnothing$ | 15.733 mm           |
| External $\varnothing$                  | 43 mm               |
| Type of product                         | Drill chuck keyless |

