

ALBRECHT
Präzisions Spannfutter

High-performance self-tightening drill chuck, Type: 65/12



Order data

Order number	341000 65/12
GTIN	4045197308306
Item class	33A

Description

Version:

High performance precision three-jaw drill chucks. High concentricity, keyless, self-tightening, high clamping force. Easily released by hand. Wearing parts hardened and exchangeable.

Application:

For bench and pillar drilling machines, milling machines, lathes, for use with arbors No. 342300 – 342850 or directly on machine spindles.

Standard:

DIN 238

Technical description

Drill chuck taper	B 12
Type	65/12
Drill head length closed	68 mm
Drill head length open	61.5 mm
largest drill chuck taper \varnothing	12.056 mm
Clamping range	0.5 - 6.5 mm
External \varnothing	34 mm
Type of product	Drill chuck keyless

