



High-performance self-tightening drill chuck Spiro, Type: 130



Order data

Order number	341010 130
GTIN	4019208009421
Item class	39R

Description

Version:

High performance precision three-jaw drill chucks. High concentricity, keyless, self-tightening, high clamping force. Easily released by hand. Wearing parts hardened and exchangeable.

Application:

For bench and pillar drilling machines, milling machines, lathes, for use with arbors No. 342300 – 342850 or directly on machine spindles.

Standard:

DIN 238

Technical description

Drill head length closed	103 mm
Drill head length open	90.5 mm
Type	130
Clamping range	1 - 13 mm
Drill chuck taper	B 16
largest drill chuck taper \varnothing	15.733 mm
External \varnothing	50 mm
Type of product	Drill chuck keyless

