

ALBRECHT
Präzisions Spannfutter

High-performance self-tightening drill chuck, Type: 100/12



Order data

Order number	341000 100/12
GTIN	4045197308320
Item class	33A

Description

Version:

High performance precision three-jaw drill chucks. High concentricity, keyless, self-tightening, high clamping force. Easily released by hand. Wearing parts hardened and exchangeable.

Application:

For bench and pillar drilling machines, milling machines, lathes, for use with arbors No. 342300 – 342850 or directly on machine spindles.

Standard:

DIN 238

Technical description

largest drill chuck taper \emptyset	12.056 mm
Drill chuck taper	B 12
Clamping range	0.5 - 10 mm
Drill head length open	80 mm
Type	100/12
Drill head length closed	91.5 mm
External \emptyset	43 mm
Type of product	Drill chuck keyless

