

**Paper masking tape set, Width×length (mm× m): 50X50****Order data**

Order number	083645 50X50
GTIN	4005801208538
Item class	08M

Description**Version:**

The **tesakrepp® 4329** is a **thin and flexible soft crepe paper masking tape**, with high wet abrasion resistance and **good paint and filler restraint**. Furthermore it is also suitable for general **masking and painting work** at temperatures up to 70°C.

Note:

The specified "best before" date for tesa® products is in relation to compliance with the specified storage guidelines.

Technical description

Width	50 mm
Manufacturer's designation	tesakrepp® 4329
Thickness	0.13 mm
Colour	yellowish
Length	50 m
Stretch capability	10 %

Liner present	no
Number of adhesive tapes	6
Tensile strength	0.33 N/mm
Adhesive	Natural rubber
temperature-resistant up to	70 °C
Storage humidity	50 - 70 %
Storage temperature	15 - 35 °C
Special features	repulpable
Special features	tearable by hand
Special features	can be written on
Backing material	Paper
Adhesive strength on steel	0.28 N/mm
Application	Masking work
Type of adhesive tape	single-sided
Type of product	Adhesive tape