

**Paper masking tape set, Width×length (mm× m): 19X50****Order data**

Order number	083645 19X50
GTIN	4005801208446
Item class	08M

Description**Version:**

The **tesakrepp® 4329** is a **thin and flexible soft crepe paper masking tape**, with high wet abrasion resistance and **good paint and filler restraint**. Furthermore it is also suitable for general **masking and painting work** at temperatures up to 70°C.

Note:

The specified "best before" date for tesa® products is in relation to compliance with the specified storage guidelines.

Technical description

Width	19 mm
Length	50 m
Thickness	0.13 mm
Manufacturer's designation	tesakrepp® 4329
Colour	yellowish
Backing material	Paper

Special features	can be written on
Special features	tearable by hand
Special features	repulpable
Tensile strength	0.33 N/mm
Liner present	no
Storage humidity	50 - 70 %
temperature-resistant up to	70 °C
Storage temperature	15 - 35 °C
Stretch capability	10 %
Number of adhesive tapes	16
Adhesive	Natural rubber
Application	Masking work
Adhesive strength on steel	0.28 N/mm
Type of adhesive tape	single-sided
Type of product	Adhesive tape