

**Garant****Self-tightening drill chuck, Type: 160/18****Order data**

Order number	341250 160/18
GTIN	4045197152831
Item class	31K

**Description****Version:**

**High performance** precision three-jaw drill chucks. High concentricity, keyless, self-tightening, high clamping force. Easily released by hand. Wearing parts hardened and exchangeable.

**Application:**

For bench and pillar drilling machines, milling machines, lathes, for use with arbors No. 342300 – 342850 or directly on machine spindles.

**Standard:**

**DIN 238**

**Technical description**

Type	160/18
Clamping range	3 - 16 mm
largest drill chuck taper Ø	17.431 mm
Drill head length open	95.5 mm
Drill chuck taper	B 18 stub
Drill head length closed	109 mm
External Ø	56 mm
Type of product	Drill chuck keyless

