

HOLEX**Straight shank drill chuck arbor, Shank Ø / drill chuck taper: 8/10mm****Order data**

Order number	342300 8/10
GTIN	4045197294388
Item class	32X

Description**Version:**

Through hardened and ground. High long-term concentricity because swarf cannot be pressed into the hardened surface and no notches can occur from minor impacts.

High precision version with plain shank.

Application:

For mounting drill chucks on to milling machines, automatic system etc. The plain shank can be clamped in a **collet or in a milling chuck**.

Standard:

Bohrfutterkegel **DIN 238**.

Technical description

Plain shank length	35 mm
Taper Ø D	10.094 mm
Drill chuck taper DIN 238	B 10
Shank Ø	8 mm
Type of product	Drill chuck adapter