



Face mill arbor with cooling channel bore Form ADB, BT 40 short, Spigot Ø d1: 40mm



Order data

Order number	303020 40
GTIN	4250122614227
Item class	36E

Description

Version:

Taper shank, spigots, and contact surfaces ground on collar.
All shanks burnished.

Supplied with:

Lock screw

Optional extras:

Pull studs (PS) No. 308760 – 308802. Special toggle spanner No. 309840.

Technical description

Spare milling cutter lock screw No. 309860 / 309861	40
Spigot Ø d ₁	40 mm
Suitable toggle spanner No. 309840	40
Overhang dimension A	50 mm
External Ø D	88 mm
Clamping Ø D ₁	40 mm
Adapter	BT 40 short
Standard	DIN 6357
Arbor standard	ISO 7388-2

Arbor standard	JIS B6339
Shape	ADB
Cooling channel bore	not pluggable
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 5 µm
Machining strategy	HPC
Type of product	Milling head arbor

Accessories

Pull stud 90°sealed suitable for steep tapers 40	308790 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Milling cutter lock screw for mandrel Ø 40 mm	309860 40
Toggle spanner for mandrel Ø 40 mm	309840 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40