

**Fabric adhesive tape, silver, Width×length (mm× m): 48X50****Order data**

Order number	083600 48X50
GTIN	4042448392954
Item class	08M

Description**Version:**

tesa® 4662 duct tape bonds with excellent adhesive strength even on rough and dusty substrates. It is waterproof, supple and flexible. Ideal for sealing pipes and cables, and for applications on plasterwork and masonry. It can easily be torn by hand both across and along the tape.

Note:

The specified "best before" date for tesa® products is in relation to compliance with the specified storage guidelines.

Technical description

Length	50 m
Thickness	0.23 mm
Manufacturer's designation	duct tape 4662
Width	48 mm
Colour	silver

Stretch capability	18 %
Storage humidity	50 - 70 %
temperature-resistant up to	95 °C
Storage temperature	15 - 35 °C
Type of adhesive tape	single-sided
Liner present	no
Special features	water-repellent
Special features	supple
Special features	tearable by hand
Fabric fineness	27 mesh
Tensile strength	3 N/mm
Adhesive	Natural rubber
Backing material	Fabric
Application	Attaching
Application	Sealing
Application	Binding
Application	Securing
Application	Packing
Application	Bonding
Adhesive strength on steel	0.44 N/mm
Product name attribute	silver
Type of product	Adhesive tape