

**PVC adhesive tape, Colour: WHITE****Order data**

Order number	083636 WHITE
GTIN	2050001661432
Item class	08M

Description**Version:**

The **3M™ 764i** can be used for non-critical application areas, such as colour marking and bundling. It is corrosion-resistant, flexible, supple, easy to apply and resistant to moisture. The 3M™ coloured marking and floor marking tapes are ideally suited for use in situations of building maintenance and for improving safety within the plant. The special structure of the coloured PVC adhesive tapes resists scratching, abrasion, weather and most chemicals. Easy to apply, very supple even on uneven surfaces.

Note:

The specified "best before" date for 3M™ products is in relation to compliance with the specified storage guidelines.

Technical description

Colour	white
Length	33 m
Width	50 mm
Manufacturer's designation	764i

Thickness	0.125 mm
Type of adhesive tape	single-sided
Stretch capability	180 %
Adhesive	Natural rubber
Working life after date of manufacture	12 mo
Backing material	PVC film
temperature-resistant up to	29 °C
Storage temperature	20 - 23 °C
Special features	supple
Special features	corrosion-resistant
Special features	moisture-resistant
Special features	abrasion resistant
Liner present	no
Tensile strength	2.28 N/mm
Adhesive strength on steel	0.21 N/mm
Application	Closing
Application	Marking
Application	Binding
Storage humidity	50 - 60 %
Type of product	Adhesive tape