



ER collet, ER 20, Nominal clamping \varnothing d: 11 mm



Order data

| | |
|--------------|---------------|
| Order number | 308930 11 |
| GTIN | 4045197151308 |
| Item class | 32Z |

Description

Version:

Through hardened and ground. Polished.

Note:

The **collet clamping \varnothing range** is always up to 1 mm less than nominal, e.g. \varnothing 10 – 9 mm, except for \varnothing 1, 1.5 and 2 (where it is only 0.5 mm).

Technical description

| | |
|----------------------------------|-----------------------|
| Nominal clamping \varnothing d | 11 mm |
| Adapter | ER 20 |
| Standard | ISO 15488-B |
| Concentricity | $\leq 10 \mu\text{m}$ |
| Type | 428 E |
| External \varnothing D | 21 mm |
| Overall length L | 31.5 mm |
| Type of product | Collet |

