



Face mill arbor with cooling channel bore Form ADB, BT 50 A = 100, Spigot Ø d1: 27mm



Order data

Order number	303045 27
GTIN	4250122616306
Item class	36E

Description

Version:

Taper shank, spigots, and contact surfaces ground on collar.
All shanks burnished.

Supplied with:

Lock screw

Optional extras:

Pull studs (PS) No. 308760 – 308802. Special toggle spanner No. 309840.

Technical description

Spare milling cutter lock screw No. 309860 / 309861	27
Spigot Ø d ₁	27 mm
Overhang dimension A	100 mm
Suitable toggle spanner No. 309840	27
External Ø D	58 mm
Clamping Ø D ₁	27 mm
Adapter	BT 50 A = 100
Standard	DIN 6357
Arbor standard	ISO 7388-2

Arbor standard	JIS B6339
Shape	ADB
Cooling channel bore	not pluggable
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 5 µm
Machining strategy	HPC
Type of product	Milling head arbor

Accessories

Pull stud 45°sealed suitable for steep tapers 50	308765 50
Pull stud 60°sealed suitable for steep tapers 50	308785 50
Pull stud 90°sealed suitable for steep tapers 50	308790 50
Toggle spanner for mandrel Ø 27 mm	309840 27
Pull stud 90°sealed suitable for steep tapers 50	308795 50
Milling cutter lock screw for mandrel Ø 27 mm	309860 27
Pull stud 45°sealed suitable for steep tapers 50	308760 50