



Set of face drivers in a wooden box right-hand, Morse taper: 6



Order data

Order number	327450 6
GTIN	4019208021195
Item class	35R

Description

Version:

- **Point angle 60°, clamping Ø 8 - 80 mm.**
- **A pre-loaded axially adjustable disc spring pack compensates for differences in centre depths.**
- **The centre can be reground easily.**

Application:

For mounting in the headstock taper of the lathe.

Supplied with:

1 base body No. 327520 (for clockwise and anticlockwise rotation),

1 centre No. 327660, 6 mm Ø, for driver head size 13 - 24,

1 centre No. 327660, 12 mm Ø, for driver head size 21 - 40,

4 driver heads for working range Ø 13 – 100 mm (No. 327600 and 327610: Sizes 13 – 24, 21 – 40, 33 – 64; No. 327640 and 327650: Sizes 51 – 100).

Supplied in a wooden box with space for another 6 driver heads and 3 centres (for the complete working range Ø 9 - 160 mm).

Note:

Counterpart to 321750 and 321770.

Working range Ø: 13 - 100 mm

Centre tip Ø: 6 / 12 mm

Weight: 6.6 kg

Technical description

Centre tip Ø	6 / 12 mm
Working range Ø	13 - 100 mm
Weight	6.6 kg
Morse taper	6
Type of product	Face driver