

**Precision masking tape, Width×length (mm× m): 30X50****Order data**

Order number	083648 30X50
GTIN	4042448816115
Item class	08M

Description**Version:**

tesakrepp® 4334 has an extra thin and tear-resistant paper carrier. It offers good positioning capability and is suitable for up to 8 weeks outdoors, for high-quality **puttying, painting, and varnishing work, giving sharp edges to paint and varnish**. It can be used on a wide variety of sensitive surfaces such as glass, aluminium, HPVC and wood.

Note:

The specified "best before" date for tesa® products is in relation to compliance with the specified storage guidelines.

Technical description

Length	50 m
Thickness	0.09 mm
Manufacturer's designation	tesakrepp® 4334
Width	30 mm
Colour	yellowish

Liner present	no
Number of adhesive tapes	1
Adhesive	Acrylate
temperature-resistant up to	120 °C
Special features	UV-resistant
Special features	can be torn by hand
Special features	can be written on
Tensile strength	0.3 N/mm
Backing material	Paper
Storage temperature	15 - 35 °C
Storage humidity	50 - 70 %
Stretch capability	4 %
Application	Masking work
Adhesive strength on steel	0.19 N/mm
Type of adhesive tape	single-sided
Type of product	Adhesive tape