

Garant
HSK coolant tube, for HSK: 50

Order data

Order number	309880 50
GTIN	4045197273925
Item class	39Z

Description
Version:

Special O-ring up to 120 bar, angular movement from $\pm 1^\circ$, polished, with 2 sealing rings.

Coolant-resistant Viton® seals.

- **Fine polished surface, hardened and burnished.**
- **Two polished transition radii.**
- **Full movement thanks to two O-rings.**
- **Hardened threaded sleeves with rolled, high-compression thread flanks.**

Description:

HSK coolant pipe – a small component with a big effect! When tools are changed thousands of times per day, it is important that the interface between the coolant pipe and machine spindle seal remains clean and, above all, that it maintains process reliability.

Suitable for:

HSK tool holders.

Technical description

Overall length L	33 mm
Thread M	M16×1
Ø D	10 mm
suitable for arbor	HSK 50
maximum pressure	120 bar

Angular movement	±1 degrees
Surface treatment	polished
Type of product	Coolant tube

Accessories

Socket wrench for coolant tubes for HSK 50	309890 50
--	-----------