


Garant
KNUX 160410L, Grade: HB7120-1

Order data

Order number	251078 HB7120-1
GTIN	4045197819918
Item class	21G

Description

KNUX 160410L HB7120-1 Grade: HB7120-1

Chip breaker: VG

Chip diverter: 3.2 mm

Cutting depth a_p : 1 - 6 mm

Feed f : 0.2 - 0.5 mm/rev.

Cutting speed v_c main application: 70 - 240 m/min

Technical description

Main application	M
Cutting conditions	continuous
Cutting depth a_p	1 - 6 mm
Feed f	0.2 - 0.5 mm/rev.
Chip diverter	3.2 mm
Chip breaker	VG
Grade	HB7120-1
Corner radius	1 mm
Cutting speed v_c main application	70 - 240 m/min
Finishing/roughing assignment	Roughing

Tool material	Carbide
Number of changes/inserts	2
ISO code indexable insert	KNUX 160410L
Type of product	Indexable insert for turning