

Arbor spacer ring, narrow, Inner \varnothing ×thickness b1: 27X0,04mm**Order data**

Order number	309920 27X0,04
GTIN	4045197306814
Item class	37D

Description**Version:**

0.03 to 1 mm wide. Cut from hardened strip steel. Variation from the width b1 and its parallelism depends on the tolerance of the basic semi-finished product to DIN 1544.

Technical description

Thickness b ₁	0.04 mm
External \varnothing	39 mm
Internal \varnothing	27 mm
Version	narrow
Standard	DIN 2084
Type of product	Arbor spacer ring