

Arbor spacer ring, narrow, Inner \varnothing ×thickness b1: 40X0,2mm**Order data**

| | |
|--------------|---------------|
| Order number | 309920 40X0,2 |
| GTIN | 4045197307026 |
| Item class | 37D |

Description**Version:**

0.03 to 1 mm wide. Cut from hardened strip steel. Variation from the width b1 and its parallelism depends on the tolerance of the basic semi-finished product to DIN 1544.

Technical description

| | |
|--------------------------|-------------------|
| Thickness b ₁ | 0.2 mm |
| External \varnothing | 54 mm |
| Internal \varnothing | 40 mm |
| Version | narrow |
| Standard | DIN 2084 |
| Type of product | Arbor spacer ring |