

**Arbor spacer ring, narrow, Inner  $\varnothing$ ×thickness b1: 27X0,05mm****Order data**

|              |                |
|--------------|----------------|
| Order number | 309920 27X0,05 |
| GTIN         | 4045197306821  |
| Item class   | 37D            |

**Description****Version:**

0.03 to 1 mm wide. Cut from hardened strip steel. Variation from the width b1 and its parallelism depends on the tolerance of the basic semi-finished product to DIN 1544.

**Technical description**

|                          |                   |
|--------------------------|-------------------|
| Thickness b <sub>1</sub> | 0.05 mm           |
| External $\varnothing$   | 39 mm             |
| Internal $\varnothing$   | 27 mm             |
| Version                  | narrow            |
| Standard                 | DIN 2084          |
| Type of product          | Arbor spacer ring |