



Base body for face driver for clamping in the chuck



Order data

Order number	327540
GTIN	4019208019895
Item class	35R

Description

Version:

- Point angle 60°, clamping \varnothing 8 - 80 mm.
- A pre-loaded axially adjustable disc spring pack compensates for differences in centre depths.
- The centre can be reground easily.
- Without centre and driver heads.
- All driver heads No. 327600 – 327650 and centres No. 327660 fit base bodies sizes 3 – 6.
- For clockwise and anticlockwise rotation.

Application:

For mounting in the headstock taper of the lathe.

Note:

Counterpart to 321750 and 321770.

Shank \varnothing : 25 mm

Clamping shank length: 45 mm

Clamping capacity \varnothing : 85 mm

Weight: 2.3 kg

Technical description

Clamping shank length	45 mm
Weight	2.3 kg
Shank \varnothing	25 mm

Clamping capacity Ø	85 mm
Type of product	Face driver