

**Fabric adhesive tape, black, Width×length (mm× m): 48X50****Order data**

Order number	083601 48X50
GTIN	4042448392961
Item class	08M

Description**Version:**

tesa® 4662 duct tape bonds with excellent adhesive strength even on rough and dusty substrates. It is waterproof, supple and flexible. Ideal for sealing pipes and cables, and for applications on plasterwork and masonry. It can easily be torn by hand both across and along the tape.

Note:

The specified "best before" date for tesa® products is in relation to compliance with the specified storage guidelines.

Type of adhesive tape: single-sided

Adhesive: Natural rubber

Thickness: 0.23 mm

Technical description

Length	50 m
Width	48 mm
Thickness	0.23 mm

Colour	black
Manufacturer's designation	duct tape 4662
Fabric fineness	27 mesh
temperature-resistant up to	95 °C
Storage temperature	15 - 35 °C
Adhesive	Natural rubber
Storage humidity	50 - 70 %
Backing material	Fabric
Type of adhesive tape	single-sided
"Best before" date	12 mo
Liner present	no
Special features	water-repellent
Special features	supple
Special features	can be torn by hand
Stretch capability	18 %
Tensile strength	3 N/mm
Adhesive strength on steel	0.44 N/mm
Application	Attaching
Application	Sealing
Application	Binding
Application	Securing
Application	Packing
Application	Bonding
Product name attribute	black
Type of product	Adhesive tape