

3M**Self-sealing insulating tape, Width×length (mm× m): 19X9****Order data**

Order number	083655 19X9
GTIN	7891040003860
Item class	08M

Description**Version:**

The **3M Scotch® 23** is an ozone-resistant ethylene-propylene-rubber adhesive tape. It has outstanding dielectric characteristics, is ozone-resistant and is compatible with all cable sheathing materials.

Note:

The specified "best before" date for 3M™ products is in relation to compliance with the specified storage guidelines.

Thickness: 0.76 mm

Technical description

Width	19 mm
Thickness	0.76 mm
Length	9 m
Stretch capability	1000 %
Colour	black

Manufacturer's designation	Scotch® 23
Type of adhesive tape	single-sided
Application	Insulating
Application	Sealing
Storage humidity	50 - 60 %
Backing material	Ethylene-propylene rubber
Special features	UV-resistant
Special features	weatherproof
Special features	moisture-resistant
Storage temperature	20 - 23 °C
"Best before" date	5 mo
temperature-resistant up to	90 - 130 °C
Tensile strength	1.4 N/mm
Liner present	yes
Type of product	Adhesive tape