



## Short drill chuck Form A, BT 40, Clamping range: 0,5-13mm



### Order data

Order number	303197 0,5-13
GTIN	2050001701251
Item class	33W

### Description

#### Version:

For clockwise and anticlockwise rotation.

#### Supplied with:

**Clamping wrench.**

#### Optional extras:

Pull studs (PS) No. 308760 – 308806. Pull stud wrenches No. 308820; 308835.

### Technical description

Clamping range	0.5 - 13 mm
Overhang dimension A	98 mm
Spare chuck key No. 627425	6 AF
External Ø D	50 mm
Adapter	BT 40
Arbor standard	JIS B6339
Arbor standard	ISO 7388-2
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 30 µm
Type of product	Short drill chuck

---

## Accessories

Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Hexagon screwdriver, with T-handle Hexagon 6 mm	627481 6
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40