

Garant**CC.T 120404, Grade: HB7120-1**

Order data

Order number	260064 HB7120-1
GTIN	4045197817143
Item class	21G

Description

CC.T 120404 HB7120-1 Grade: HB7120-1
Chip breaker: VS
Tolerance: M
Cutting depth a_p : 0.2 - 2.5 mm
Feed f : 0.1 - 0.3 mm/rev.
Cutting speed v_c main application: 90 - 290 m/min

Technical description

Grade	HB7120-1
Cutting speed v_c main application	90 - 290 m/min
Chip breaker	VS
Main application	M
Feed f	0.1 - 0.3 mm/rev.
Cutting depth a_p	0.2 - 2.5 mm

Cutting conditions	continuous
Corner radius	0.4 mm
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	CCMT 120404
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning