

**Garant**
**Shrink-fit chuck Form ADB, BT 40 short, Clamping range  $\varnothing$  D1: 25mm**

**Order data**

Order number	303410 25
GTIN	4045197467898
Item class	31A

**Description**
**Version:**

- Integral tool length adjustment, range 10 mm (from  $\varnothing$  6).
- Size 3-5 for carbide, from size 6 for HSS and carbide.

**Application:**

For clamping tools with parallel shank to h6 tolerance.

**Standard:**

**Ähnlich E-DIN 69882-8, Form G.**

**Optional extras:**

Pull studs (PS), No. 308760 – 308806, shrink-fit chuck extension No. 302410 – 302417, shrink-fit units No. 354210 – 354400.

**Technical description**

$\varnothing$ D <sub>2</sub>	44 mm
Overhang dimension A	100 mm
Clamping $\varnothing$ D <sub>1</sub>	25 mm
External $\varnothing$ D	53 mm
Adapter	BT 40 short
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Shape	ADB

Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Machining strategy	HPC
Type of product	Shrink-fit chuck

## Accessories

Screening plate for coilSU1 for clamping Ø 20-32 mm	354240 20-32
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Basic tool mountingfor SK for SK taper shank 40	354225 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Cooling unit Type CU1	354215 CU1
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Cooling adapter long4.5° for clamping Ø 22,1-32 mm	354236 22,1-32
Cooling adapter short4.5° for clamping Ø 22,1-32 mm	354235 22,1-32
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Shrink-fit unit Type SU1	354210 SU1
Pull stud 90°sealed suitable for steep tapers 40	308790 40