



Angle grinder, Type: AGV17-150



Order data

Order number	077141 AGV17-150
GTIN	4002395243990
Item class	03M

Description

Version:

Milwaukee angle grinder with smooth start-up, **restart inhibit** and overload protection. 1750 W / 150 mm angle grinder with **constant-speed electronics**, anti-kickback function, **anti-vibration handle**, disc change without using tools. **FIXTEC** clamping nut.

Supplied with:

Additional handle, guard cover, 4 m power cable.

Technical description

Power consumption	1750 W
maximum vibration to EN	8.7 m/s ²
Kick-back stop	yes
maximum cutting depth	45 mm
Soft start	yes
Restart block	yes
maximum disc Ø	150 mm
Weight	3 kg
Manufacturer's designation	AGV17-150XCProTector/ dead-man's switch
Power supply	Mains operated

maximum speed	9500 min ⁻¹
Type of product	Angle grinder

Accessories

Clamping nut M14 Type NUT	073930 NUT
Clamping nut M14 Type FIXTEC	073930 FIXTEC