

Garant
Shrink-fit chuck Form ADB, BT 40 short, Clamping range \varnothing D1: 5mm

Order data

Order number	303410 5
GTIN	4045197467805
Item class	31A

Description
Version:

- Integral tool length adjustment, range 10 mm (from \varnothing 6).
- Size 3-5 for carbide, from size 6 for HSS and carbide.

Application:

For clamping tools with parallel shank to h6 tolerance.

Standard:

Ähnlich E-DIN 69882-8, Form G.

Optional extras:

Pull studs (PS), No. 308760 – 308806, shrink-fit chuck extension No. 302410 – 302417, shrink-fit units No. 354210 – 354400.

Technical description

\varnothing D ₂	12 mm
Clamping \varnothing D ₁	5 mm
Overhang dimension A	90 mm
External \varnothing D	17 mm
Adapter	BT 40 short
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Shape	ADB

Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Machining strategy	HPC
Type of product	Shrink-fit chuck

Accessories

Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Shrink-fit unit Type SU1	354210 SU1
Cooling adapter short 4.5° for clamping Ø 3-5,9 mm	354235 3-5,9
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Cooling adapter long 4.5° for clamping Ø 3-5,9 mm	354236 3-5,9
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Cooling unit Type CU1	354215 CU1
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Screening plate for coil SU1 for clamping Ø 3-5 mm	354240 3-5
Basic tool mounting for SK for SK taper shank 40	354225 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Subframe cupboard	354290