

**Fabric adhesive tape stabilised, Width×length (mm× m): 38X25****Order data**

Order number	083605 38X25
GTIN	4042448141361
Item class	08M

Description**Version:**

tesa® 53799 exhibits very good adhesive strength even on rough substrates. It can be torn by hand easily and cleanly, is water-repellent, weather-resistant, resists heavy weights and is very supple. Thus it is ideal for a wide range of repair work and construction work, and also for packaging, bundling, bonding, etc.

Note:

The specified "best before" date for tesa® products is in relation to compliance with the specified storage guidelines.

Technical description

Colour	red
Manufacturer's designation	53799
Width	38 mm
Thickness	0.31 mm
Length	25 m

Special features	supple
Special features	can be torn by hand
Special features	abrasion resistant
Adhesive	Natural rubber
temperature-resistant up to	110 °C
Liner present	no
Tensile strength	7.7 N/mm
Storage temperature	15 - 35 °C
Storage humidity	50 - 70 %
Type of adhesive tape	single-sided
Backing material	Fabric
Fabric fineness	80 mesh
Stretch capability	11 %
Application	Joining
Application	Packing
Application	Binding
Application	Covering
Application	Bonding
Adhesive strength on steel	0.47 N/mm
Type of product	Adhesive tape