

3M**Filament adhesive tape, Width×length (mm× m): 25X50**

Order data

Order number	083666 25X50
GTIN	2050001712363
Item class	08M

Description

Version:

3M™ 8954 is made of PP with **high-tensile glass fibre-reinforcement (across and along)** with very high tear resistance and abrasion resistance. **Suitable for packaging hazardous goods for transport!**

Application:

For binding and securing, e.g. for securing pallets or products.

Note:

The specified "best before" date for 3M™ products is in relation to compliance with the specified storage guidelines.

Technical description

Width	25 mm
Manufacturer's designation	8954
Colour	transparent
Length	50 m

Thickness	0.13 mm
Type of adhesive tape	single-sided
"Best before" date	12 mo
Adhesive strength on steel	0.7 N/mm
Adhesive	Synthetic rubbers
Application	Bonding
Application	Binding
Application	Packing
Stretch capability	10 %
Storage temperature	21 °C
Tensile strength	13.5 N/mm
temperature-resistant up to	60 °C
Special features	tear-resistant
Special features	moisture-resistant
Special features	abrasion resistant
Liner present	no
Storage humidity	50 %
Backing material	PP film
Type of product	Adhesive tape