

Arbor spacer ring, wide, Inner Ø×thickness b1: 22X60mm**Order data**

Order number	309930 22X60
GTIN	4045197307279
Item class	37D

Description**Version:**

2.0 – 60 mm wide. Made of case-hardening steel, hardened. External Ø ground, flat surfaces lapped. Permissible variation in parallelism for the width is IT 3, referred to bore dia. d1. Tolerance of the ring width ± 0.1 mm.

Technical description

Thickness b ₁	60 mm
External Ø	34 mm
Internal Ø	22 mm
Version	wide
Standard	DIN 2084
Type of product	Arbor spacer ring