

**Arbor spacer ring, wide, Inner Ø×thickness b1: 16X20mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 309930 16X20  |
| GTIN         | 4045197307170 |
| Item class   | 37D           |

**Description****Version:**

2.0 – 60 mm wide. Made of case-hardening steel, hardened. External Ø ground, flat surfaces lapped. Permissible variation in parallelism for the width is IT 3, referred to bore dia. d1. Tolerance of the ring width  $\pm 0.1$  mm.

**Technical description**

|                          |                   |
|--------------------------|-------------------|
| Thickness b <sub>1</sub> | 20 mm             |
| External Ø               | 27 mm             |
| Internal Ø               | 16 mm             |
| Version                  | wide              |
| Standard                 | DIN 2084          |
| Type of product          | Arbor spacer ring |