



Angle grinder Deadman, Type: 72211129



Order data

Order number	077152 72211129
GTIN	4014586853314
Item class	03F

Description

Version:

- **FEIN high power motor with enormous traction power for high removal rates.**
- **Automatic restart inhibit after power supply interruption.**
- **Rear handle can be turned to 4 positions.**

Dead man's switch, i.e. can be operated only when both hands are on the machine. Without locking On / Off switch.

- **Non-wearing EBS electrical braking system stops the machine in less than 3 seconds.**
- **FEIN quick-release clamping system QuickIN for quick easy and reliable disc changes without using tools.**

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

Supplied with:

Supplied with protective hood, additional handle, clamping set.

Manufacturer's designation: WSB25-230X

Power consumption: 2500 W

maximum speed: 6,600 min⁻¹

maximum disc \varnothing : 230 mm

maximum cutting depth: 66 mm

Weight: 5.4 kg

Technical description

Weight	5.4 kg
--------	--------

Dead man's circuit	yes
maximum vibration to EN	6 m/s ²
Power consumption	2500 W
Manufacturer's designation	WSB25-230X
Special features	QuickIN
maximum cutting depth	66 mm
maximum disc Ø	230 mm
maximum speed	6,600 min ⁻¹
Power supply	Mains operated
Type of product	Angle grinder