

**Arbor spacer ring, wide, Inner Ø×thickness b<sub>1</sub>: 16X3mm****Order data**

Order number	309930 16X3
GTIN	4045197307125
Item class	37D

**Description****Version:**

2.0 – 60 mm wide. Made of case-hardening steel, hardened. External Ø ground, flat surfaces lapped. Permissible variation in parallelism for the width is IT 3, referred to bore dia. d<sub>1</sub>. Tolerance of the ring width ± 0.1 mm.

**Technical description**

Thickness b <sub>1</sub>	3 mm
External Ø	27 mm
Internal Ø	16 mm
Version	wide
Standard	DIN 2084
Type of product	Arbor spacer ring