

3M**Insulating tape, 15 mm×10 m, Colour: BLUE****Order data**

Order number	083652 BLUE
GTIN	4054596613492
Item class	08M

Description**Version:**

3M™ Temflex® 165 is a **general-purpose soft PVC insulating tape**. Flame resistant. Self-extinguishing, good resistance to oil and solvents.

Application:

For insulating, binding, securing, and colour marking.

Note:

The specified "best before" date for 3M™ products is in relation to compliance with the specified storage guidelines.

Technical description

Manufacturer's designation	3M® Temflex® 165
Length	10 m
Width	15 mm
Thickness	0.15 mm
Colour	blue

Tensile strength	2 N/mm
Backing material	PVC film
Adhesive strength on steel	0.2 N/mm
Type of adhesive tape	single-sided
Storage humidity	50 - 60 %
Liner present	no
temperature-resistant up to	90 °C
Application	Identification
Application	Insulating
Application	Binding
Application	Marking
Stretch capability	200 %
Storage temperature	20 - 23 °C
Product name attribute	15 mm×10 m
Type of product	Adhesive tape